



1-Gang Masonry Box, Nongangable, 2-1/2 in. Deep, Eight Concentric KO's

By Raco
Catalog # 690



1-Gang Masonry Box, Nongangable, 2-1/2 in. Deep, Eight
Concentric KO's

Features

- Rugged welded design does not fall apart during construction.
- Available from one to six gang configurations in both 2-1/2" and 3-1/2" depths.
- Rectangular shape fits square cuts in block.
- Large volume design allows for additional work room inside the box.
- Standard 1/2" and 3/4" concentric knockouts.
- Device ears inside the box prevent mortar from getting in the device holes.
- Steel voltage partition #971 fits all 2-1/2" or 3-1/2" depths.
- Standard wall plates can be used.
- Supplied with eight 1/2 & 3/4 in. concentric knockouts
- Welded steel construction
- Standard device spacing with tapped 6-32 holes for devices
- 16 cu. in. capacity
- For 4 in. block walls

General

Bracket Type	No Bracket
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Gangable	No
Knockouts	1/2 - 3/4 in Concentric
Material	Steel
Number of Gang(s)	1-Gang
Type	<ul style="list-style-type: none">• Box• Box
UPC	050169006900
Wiring System	Conduit

Dimensions

Cubic Capacity	16 cu.in
Depth	2.5 in
Height	3.75 in
Weight	0.63 lb
Width	1.969 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	2250

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-9](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-690-SPEC-EN | REV 6/2024

