



## 5-Gang Masonry Box, Nongangable, 2-1/2 in. Deep, Nineteen Concentric KO's

By Raco  
Catalog # [694](#)



5-Gang Masonry Box, Nongangable, 2-1/2 in. Deep, Nineteen Concentric KO's

### Features

- Rugged welded design does not fall apart during construction.
- Available from one to six gang configurations in both 2-1/2" and 3-1/2" depths.
- Rectangular shape fits square cuts in block.
- Large volume design allows for additional work room inside the box.
- Standard 1/2" and 3/4" concentric knockouts.
- Device ears inside the box prevent mortar from getting in the device holes.
- Steel voltage partition #971 fits all 2-1/2" or 3-1/2" depths.
- Standard wall plates can be used.

### General

Bracket Type	No Bracket
Catalog Number	694
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Gangable	No
Knockouts	1/2 - 3/4 in Concentric
Material	Steel
Number of Gang(s)	5-Gang
Type	Box
UPC	050169006948
Wiring System	Conduit

### Dimensions

Cubic Capacity	79.5 cu.in
Depth	2.5 in
Height	3.75 in
Weight	1.986 lb
Width	9.219 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	10
Packaging Type	No Packaging
Pallet Quantity	800

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-9](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-694-SPEC-EN | REV 6/2024