



1-Gang BLOCK-LOC® Masonry Box, NonGangable, 3-1/2 in. Deep, Conduit KO's, Welded

By Raco
Catalog # 695B



1-Gang BLOCK-LOC® Masonry Box, NonGangable, 3-1/2 in.
Deep, Conduit KO's, Welded

Features

- Integral brackets securely hold box to concrete block from front and back in masonry block walls, even in irregular openings
- TKO® Knockouts allow for design and installation flexibility
- Supplied with ten 1/2-3/4 in.TKO® knockouts
- Quick and accurate positioning
- Break off front tabs
- Non-gangable
- 22.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Catalog Number	695B
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	1-Gang
Type	Masonry Box
	Box
UPC	050169500620

Dimensions

Cubic Capacity	22.5 cu.in
Depth	3.5 in
Height	3.797 in
Raised Ground	No
Weight	0.946 lb
Width	3.547 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	18
Pallet Quantity	1440

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-9](#)
[Sales Drawings - 695B Customer Drawing](#)
[SDS - HCC SDS](#)
[Sell Sheets - BLOCK-LOC® Masonry Boxes](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: BLOCK-LOC® Masonry Box Support](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-695B-SPEC-EN | REV 6/2024