



## 2-Gang Masonry Box, Nongangable, 3-1/2 in. Deep, Sixteen Concentric KO's

By Raco  
Catalog # 696



2-Gang Masonry Box, Nongangable, 3-1/2 in. Deep, Sixteen Concentric KO's

### Features

- Rugged welded design does not fall apart during construction.
- Available from one to six gang configurations in both 2-1/2" and 3-1/2" depths.
- Rectangular shape fits square cuts in block.
- Large volume design allows for additional work room inside the box.
- Standard 1/2" and 3/4" concentric knockouts.
- Device ears inside the box prevent mortar from getting in the device holes.
- Steel voltage partition #971 fits all 2-1/2" or 3-1/2" depths.
- Standard wall plates can be used.
- Supplied with sixteen 1/2 and 3/4 in. concentric knockouts
- Welded steel construction
- Standard device spacing with tapped 6-32 holes for devices
- 45 cu. in. capacity
- For 6, 8, and 10 in. block walls

### General

Bracket Type	No Bracket
Catalog Number	696
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Gangable	No
Knockouts	1/2 - 3/4 in Concentric
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169006962
Wiring System	Conduit

### Dimensions

Cubic Capacity	45 cu.in
Depth	3.5 in
Height	3.75 in
Weight	1.184 lb
Width	3.781 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1350

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-9](#)  
[Sales Drawings - 696 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-696-SPEC-EN | REV 6/2024