



2-Gang BLOCK-LOC® Masonry Box, NonGangable, 3-1/2 in. Deep, Conduit KO's, Welded

By Raco
Catalog # 696B



2-Gang BLOCK-LOC® Masonry Box, NonGangable, 3-1/2 in. Deep, Conduit KO's, Welded

Features

- Integral brackets securely hold box to concrete block from front and back in masonry block walls, even in irregular openings
- TKO® Knockouts allow for design and installation flexibility
- Supplied with sixteen 1/2-3/4 in. TKO® knockouts
- Quick and accurate positioning
- Break off front tabs
- Non-gangable
- 45.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Catalog Number	696B
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Masonry Box
	Box
UPC	050169500637

Dimensions

Actual Depth	3.578 in
Cubic Capacity	45 cu.in
Depth	3.5 in
Raised Ground	No

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	12
Pallet Quantity	960

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-9](#)
[Sales Drawings - 696B Customer Drawing](#)
[SDS - HCC SDS](#)
[Sell Sheets - BLOCK-LOC® Masonry Boxes](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: BLOCK-LOC® Masonry Box Support](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-696B-SPEC-EN | REV 6/2024