



## 3-Gang BLOCK-LOC® Masonry Box, NonGangable, 3-1/2 in. Deep, Conduit KO's, Welded

By Raco  
Catalog # 697B



3-Gang BLOCK-LOC® Masonry Box, NonGangable, 3-1/2 in.  
Deep, Conduit KO's, Welded

### Features

- Integral brackets securely hold box to concrete block from front and back in masonry block walls, even in irregular openings
- Supplied with nineteen 1/2-3/4 in. concentric knockouts
- Quick and accurate positioning
- Break off front tabs
- Non-gangable
- 67.3 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Catalog Number	697B
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	3-Gang
Type	Masonry Box
	Box
UPC	050169500644

### Dimensions

Actual Depth	3.578 in
Cubic Capacity	67.3 cu.in
Depth	3.5 in
Raised Ground	No

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	12
Pallet Quantity	660

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-9](#)  
[Sales Drawings - 697B Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - BLOCK-LOC® Masonry Boxes](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - RACO: BLOCK-LOC® Masonry Box Support](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-697B-SPEC-EN | REV 6/2024