



4 in. Round Nonmetallic Vapor Barrier Ceiling Box, 2-39/64 in. Deep

By Raco
Catalog # 7122RAC



4 in. Round Nonmetallic Vapor Barrier Ceiling Box, 2-39/64 in. Deep

Features

- RACO® Nonmetallic cable boxes provide the installer with a cost alternative that is lightweight and easy to install.
- Self-clamping wire entry clamps.
- Extra long, metal swing arms ensure installation.
- Wrap around metal clamp to secure box to sheetrock.

General

Bracket Type	No Bracket
Cable Clamps	4
Ceiling Fan Rated	No
Color	Gray
Fixture Type	Light
Material	Steel
Old Work or New Work	Old Work
Type	Box
UPC	050169971222
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	2.813 in
Cubic Capacity	18.0 cu.in
Depth	2.8125 in
Fixture Lbs.	6 lb
Height	4.375 in
Weight	0.225 lb
Width	4.375 in

Certifications and Compliance

Certified Listed	UL Listed
Description SPEC - Certification	Canada 1,237,515; 1,260,599.

Logistics

Carton Quantity	100
Pallet Quantity	1000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
RACO-7122RAC-SPEC-EN | REV 6/2023