



4 in. Round Non-Metallic Ceiling Box, 2-3/8 in. Deep with Expandable Bar Hanger and Ground Plate

By Raco
Catalog # 7825



4 in. Round Non-Metallic Ceiling Box, 2-3/8 in. Deep with Expandable Bar Hanger and Ground Plate

Features

- RACO® Nonmetallic cable boxes provide the installer with a cost alternative that is lightweight and easy to install.
- Self-clamping wire entry clamps.
- Round fixture boxes offer an optional front-mounted grounding screw.
- Supports up to 10 lb. fixtures - not listed for ceiling fans
- 6 self-gripping NMSC wire entry clamps are integral part of the box
- 20.0 cu. in capacity
- Assembled steel ground plate

General

Cable Clamps	6
Ceiling Fan Rated	No
Color	Black
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Light
Material	Steel
Type	Box
UPC	050169078259
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	3 in
Cubic Capacity	18 cu.in
Depth	2.375 in
Fixture Lbs.	10 lb
Height	4 in
Weight	0.643 lb
Width	15.25 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
Description SPEC - Certification	Canada 1,233,900; 1,237,515; 1,260,599.

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1050

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-7825-SPEC-EN | REV 6/2024