



3-1/2 in. Round Non-Metallic Ceiling Box, 2-5/8 in. Deep with Expandable Bar Hanger and Ground Plate



By Raco
Catalog # 7907

3-1/2 in. Round Non-Metallic Ceiling Box, 2-5/8 in. Deep with Expandable Bar Hanger and Ground Plate

Features

- RACO® Nonmetallic cable boxes provide the installer with a cost alternative that is lightweight and easy to install.
- Self-clamping wire entry clamps.
- Round fixture boxes offer an optional front-mounted grounding screw.
- Not suitable for ceiling fan installations
- Cable clamps suitable for use with steel and alum armored cable, MCI cable, MCI-A cable and flexible conduit
- 15.5 cu. in. capacity
- Maximum support load for a static fixture is 50 lbs. when supported between 16 in. centers

General

Bracket Type	No Bracket
Cable Clamps	4
Ceiling Fan Rated	No
Color	Black
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Light
Material	Steel
Type	Box
UPC	050169079072
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Cubic Capacity	18 cu.in
Depth	3.5 in
Fixture Lbs.	10 lb
Height	4.25 in
Weight	0.549 lb
Width	15.5 in

Certifications And Compliance

Certified Listed	UL Listed
Description SPEC - Certification	Canada 1,233,900; 1,237,515; 1,260,599.

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1050

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-7907-SPEC-EN | REV 6/2024