



4 in. Square Cover, Exposed Work, 1.719 in. dia. 30A Locking Receptacle

By Raco
Catalog # 811C

4 in. Square Cover, Exposed Work, 1.719 in. dia. 30A Locking
Receptacle



Features

- RACO® exposed work covers include required hardware for mounting the receptacle(s)
- RACO® exposed work covers meet the requirements of the 2014 NEC Article 250.146(A). No bonding jumper is required for covers with: (1) Crushed corners
- Hardware and cover are packed in a poly-bag with printed catalog number, compliances and installation instructions
- cULus Listed

General

EU RoHS Indicator	Yes
Material	811C
Paintable/Stainable	No
Type	Exposed Cover
UPC	050169999868

Dimensions

Cubic Capacity	6.5 cu.in
Dimensions	0.5 in x 4.188 in x 4.188 in
Height	4.188 in
Length	0.5 in
Raised Height	0.5 in
Weight	0.394 lb
Width	4.188 in

Certifications And Compliance

Certified Listed cULus Listed

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Packaging Type	Polybag
Pallet Quantity	3780

Product Assets

[Brochures - Product Solutions for Electrical Prefabrication](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Installation Manuals - RACO Crushed Corners Covers](#)
[Instruction Sheet](#)
[Product Logo - CrushCorner](#)
[Sales Drawings - 811C CUS](#)
[SDS - HCC_SDS](#)
[Sell Sheets - Exposed Work Covers](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO Crushed Corner Exposed Work Covers Review & Installation](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-811C-SPEC-EN | REV 6/2024