



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Nine 1/2 in. KO's, Raised Ground

By Raco
Catalog # 8125



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Nine 1/2 in. KO's, Raised Ground

Features

- Drawn steel construction with raised ground screw area
- 4 in. x 1-1/2 in. deep
- Supplied with nine 1/2 in. knockouts
- Combination Phillips/slotted screw heads
- 15.5 cu. in. capacity

General

Bracket Type	No Bracket
Catalog Number	8125
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	4 in
Type	Box
UPC	050169001257
Wiring System	Conduit

Dimensions

Actual Depth	1.813 in
Cubic Capacity	15.5 cu.in
Depth	1.5 in
Fixture Lbs.	50 lb
Height	3.563 in
Raised Ground	Yes
Weight	0.487 lb
Width	3.563 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	30
Packaging Type	No Packaging
Pallet Quantity	3000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 2](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 8125 Customer Drawing](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-8125-SPEC-EN | REV 6/2024