



4 in. Square Box, Drawn, 1-1/2 in. Deep with Ten 1/2 in. and Six 3/4 in. KO's, Raised Ground

By Raco
Catalog # [8192](#)



4 in. Square Box, Drawn, 1-1/2 in. Deep with Ten 1/2 in. and Six 3/4 in. KO's, Raised Ground

Features

- Ideal for exposed work applications
- Combination screw heads allow quick installation
- Drawn construction
- Ten 1/2 in. knockouts and six 3/4 in. knockouts
- UL Listed
- 21.0 cu. in. capacity
- Acceptable in 2-hour fire rated walls
- UPC barcoded

General

Bracket Type	No Bracket
Catalog Number	8192
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in.;3/4 in
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169001929
Wiring System	Conduit

Dimensions

Actual Depth	1.79 in
Cubic Capacity	21 cu.in
Depth	1.5 in

Height	4.056 in
Raised Ground	Yes
Weight	0.648 lb
Width	4.087 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	2750

Product Assets

- [360 Product View - RACO_8192](#)
- [Catalogs - Steel Boxes, Covers and Accessories](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - NEMA OS1](#)
- [Certifications - LEED Statement](#)
- [Certifications - UL COC - E195978- 2](#)
- [Sales Drawings - RACO-drawn-steel-box-infographic](#)
- [SDS - HCC SDS](#)
- [Specifications - 8192](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand