



## 4 in. Square Box, Welded, 1-1/2 in. Deep, Nine 1/2 in. KO's & Five TKO's, Flush, FH Bracket

By Raco  
Catalog # 8197

4 in. Square Box, Welded, 1-1/2 in. Deep, Nine 1/2 in. KO's & Five TKO's, Flush, FH Bracket



### Features

- TKO knockout design provides installation flexibility
- FH bracket, flush
- Welded construction
- Nine 1/2 in. knockouts and Five TKO knockouts
- UL Listed
- 21.0 cu. in. capacity
- Acceptable in 2-hour fire rated walls
- UPC barcoded

### General

Bracket Type	FH, for Wood Studs
Catalog Number	8197
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	1-Gang
Type	Box
UPC	050169001974
Wiring System	Conduit

### Dimensions

Actual Depth	1.834 in
Cubic Capacity	21 cu.in
Depth	1.5 in
Height	6.938 in
Raised Ground	No
Weight	0.783 lb
Width	4.549 in

### Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1400

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978- 3](#)  
[Sales Drawings - 8197 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-8197-SPEC-EN | REV 6/2024