



Vapor Barrier Cable Box 4-Gang, Non-Metallic

By Raco
Catalog # [82024FBAR](#)



Vapor Barrier Cable Box 4-Gang, Non-Metallic, 2-5/8 in Deep, 1/2 in Setback

Features

- For use with Nonmetallic sheathed cable
- Flanged with vapor barrier and integral wire entry seal providing superior energy savings and quick installation
- Self-Clamping wire entry clamps
- Hands free installation
- For 1/2", 5/8", 3/4" drywall

Application

Vapor barrier boxes prevent unwanted penetration of exterior air and help maintain the existing interior environment for elements outside the structure. RACO® nonmetallic vapor barrier cable boxes provide the installer a cost savings alternative that is lightweight and easy to install and provides excellent protection for wiring and devices. RACO® non-metallic cable boxes are used in branch circuit wiring to splice wires and accommodate wiring devices such as switches and receptacles.

General

| | |
|----------------|--------------|
| Catalog Number | 82024FBAR |
| UPC | 050169991084 |

Dimensions

| | |
|----------------|--------------------|
| Cubic Capacity | 152.62164225 cu.in |
| Depth | 2.625 in |
| Height | 6.438 in |
| Width | 9.031 in |

Logistics

| | |
|-----------------|-----|
| Carton Quantity | 12 |
| Pallet Quantity | 432 |

Product Assets

- [360 Product View - RACO_82024FBAR](#)
- [Brochures - Vapor Barrier Boxes](#)
- [Catalogs - Nonmetallic Cable Boxes](#)
- [Specifications - 82024FBAR](#)



A Hubbell brand