



## 4 in. Square Box, Welded, 1-1/2 in. Deep with Nine 1/2 KO's & Five TKO's, Flush, W Bracket

By Raco  
Catalog # 8208



4 in. Square Box, Welded, 1-1/2 in. Deep with Nine 1/2 KO's & Five TKO's, Flush, W Bracket

### Features

- TKO knockout design provides installation flexibility
- W style bracket, flush
- Welded construction
- Nine 1/2 in. knockouts and Five TKO knockouts
- UL Listed
- 21.0 cu. in. capacity
- Acceptable in 2-hour fire rated walls
- UPC barcoded

### General

Bracket Type	W, for Metal or Wood Studs
Catalog Number	8208
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Material	Steel
Type	Box
UPC	050169002087
Wiring System	Conduit

### Dimensions

Actual Depth	1.75 in
Cubic Capacity	21 cu.in
Depth	1.5 in
Height	6.813 in
Raised Ground	No
Weight	0.9 lb
Width	5.938 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1500

### Product Assets

[3D Product View - RACO\\_8208](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Sales Drawings - 8208 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-8208-SPEC-EN | REV 6/2024