



**4 in. Square Box, Welded, 2-1/8 in. Deep, One 1/2 in. and Twelve 3/4 in. KO's**

By Raco  
Catalog # [8231](#)



4 in. Square Box, Welded, 2-1/8 in. Deep, One 1/2 in. and Twelve 3/4 in. KO's

**Features**

- Combination screw heads allow quick installation
- Welded construction
- Eight 3/4 in. knockouts
- UL Listed
- 30.3 cu. in. capacity
- Acceptable in 2-hour fire rated walls
- UPC barcoded

**General**

Bracket Type	No Bracket
Catalog Number	8231
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in.;3/4 in
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169002315
Wiring System	Conduit

**Dimensions**

Actual Depth	2.425 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in

Height	4 in
Raised Ground	No
Weight	0.87 lb
Width	4 in

**Electrical Ratings**

Power Distribution Features	Fire Rated
-----------------------------	------------

**Certifications And Compliance**

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed

**Logistics**

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1750

**Product Assets**

- [Catalogs - Steel Boxes, Covers and Accessories](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - LEED Statement](#)
- [Certifications - NEMA OS1](#)
- [Certifications - UL COC - E195978- 2](#)
- [Sales Drawings - RACO-welded-steel-box-infographic](#)
- [SDS - HCC SDS](#)
- [Specifications - 8231](#)
- [Terms and Conditions - HCC Terms & Conditions](#)