



4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in KO's & Six TKO's, Raised Ground

By Raco
Catalog # 8232



4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in KO's & Six TKO's, Raised Ground

Features

- Combination screw heads allow quick installation
- Welded construction
- Ten 1/2 in KO's & Six TKO's
- UL Listed
- 30.3 cu. in. capacity
- Raised ground
- Acceptable in 2-hour fire rated walls
- UPC barcoded

General

Bracket Type	No Bracket
Catalog Number	8232
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169002322
Wiring System	Conduit

Dimensions

Actual Depth	2.434 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4 in

Raised Ground	Yes
Weight	0.884 lb
Width	4 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2024)
Certified Listed	UL Listed

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1750

Product Assets

- [360 Product View - RACO_8232](#)
- [Catalogs - Steel Boxes, Covers and Accessories](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - NEMA OS1](#)
- [Certifications - LEED Statement](#)
- [Certifications - UL COC - E195978- 2](#)
- [Sales Drawings - RACO-welded-steel-box-infographic](#)
- [SDS - HCC SDS](#)
- [Specifications - 8232](#)
- [Terms and Conditions - HCC Terms & Conditions](#)