



4 in. Square Box, Welded, 2-1/8 in. Deep, Nine 1/2 in. KO's and Five TKO's, TS Bracket, Flush

By Raco
Catalog # 8235

4 in. Square Box, Welded, 2-1/8 in. Deep, Nine 1/2 in. KO's and Five TKO's, TS Bracket, Flush



Features

- TS style bracket, flush
- Combination screw heads allow quick installation
- Welded construction
- Nine 1/2 in. knockouts and Five TKO knockouts
- UL Listed
- 30.3 cu. in. capacity
- Acceptable in 2-hour fire rated walls
- UPC barcoded

General

Bracket Type	TS, for Metal or Wood Studs
Catalog Number	8235
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169002353
Wiring System	Conduit

Dimensions

Actual Depth	2.402 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	7.01 in
Raised Ground	No
Weight	1.016 lb
Width	4.436 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1375

Product Assets

[Brochures - HCC Products for Solar](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 2](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 8235 Customer Drawing](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-8235-SPEC-EN | REV 6/2024