



4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in., Four 3/4 in., Four 1 in. KO's and 3 TKO's, Raised Ground

By Raco
Catalog # 8265SP



4-11/16 in. Square Box, Welded, 2-1/8 in. Deep with One 1/2 in., Four 3/4 in., Four 1 in. KO's and 3 TKO's, Raised

Features

- Combination screw heads provide for faster installation.
- TKO knockouts allow for design and installation flexibility.
- Welded steel construction
- 4-11/16 in. square x 2-1/8 in. deep
- Supplied with four (4) 3/4 in., four (4) 1 in., one (1) 1/2 in., and three (3) 1/2 & 3/4 in. TKO knockouts
- Combination Phillips/slotted screw heads
- 42.0 cu. in. capacity

General

Bracket Type	No Bracket
Color	Gray
Drawn or Welded	Welded
Knockouts	1/2 in.;3/4 in.;1 in.;1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
Wiring System	Conduit

Dimensions

Actual Depth	2.44 in
Cubic Capacity	42 cu.in
Depth	2.125 in
Height	4.688 in
Raised Ground	Yes
Weight	1.07 lb
Width	4.688 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	20
Packaging Type	No Packaging
Pallet Quantity	1280

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - LEED Statement](#)
- [Certifications - NEMA OS1](#)
- [Sales Drawings - RACO-welded-steel-box-infographic](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-8265SP-SPEC-EN | REV 6/2024