



4-11/16 in. Square Cover, 1/2 in. Raised, Open, Ears 2-3/4 in. O.C

By Raco
Catalog # 829

4-11/16 in. Square Cover, 1/2 in. Raised, Open, Ears 2-3/4 in. O.C



Features

- Maximum support load for a static fixture is 50 lbs
- Made from zinc, pre-coated, steel
- Not designed for ceiling fan support
- Angled mounting slots allows for installation of cover without removing the box screws

General

Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	829
Paintable/Stainable	No
Type	Fixture Cover
UPC	050169008294

Dimensions

Cubic Capacity	3 cu.in
Dimensions	0.5 in x 4.688 in x 4.688 in
Fixture Lbs.	50 lb
Height	4.688 in
Length	0.5 in
Raised Height	0.5 in
Weight	0.362 lb
Width	4.688 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	5000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-17](#)
[Certifications - UL COC - E195978- 9](#)
[Sales Drawings - 829](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-829-SPEC-EN | REV 6/2024