



## 3-1/2 in. Round Ceiling Pan, Drawn, 1/2 in. Deep, One 1/2 in. KO and NMSC Clamps

By Raco  
Catalog # 8292



3-1/2 in. Round Ceiling Pan, Drawn, 1/2 in. Deep, One 1/2 in. KO and NMSC Clamps

### Features

- Rated for 50 lb. fixture support
- Combination screw heads provide for faster installation
- L clamps provided for Nonmetallic Sheathed Cable (NMSC)
- Supplied with one 1/2 in. knockout
- 6.0 cu. in. capacity
- Do not use to support ceiling fans

### General

Catalog Number	8292
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	3.5 in
Type	Ceiling Pan
UPC	050169002926
Wiring System	Nonmetallic Sheathed Cable

### Dimensions

Actual Depth	0.578 in
Cubic Capacity	4 cu.in
Depth	0.5 in
Fixture Lbs.	50 lb
Height	3.375 in
Raised Ground	No
Weight	0.286 lb
Width	3.375 in

### Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

### Certifications And Compliance

Certified Listed	UL Listed
Description SPEC - Certification	Canada 1,324,360; Mexico 166,125.

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	4200

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Sales Drawings - RACO-drawn-steel-box-infographic](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-8292-SPEC-EN | REV 6/2024