



4 in. Round Ceiling Pan, Drawn, 1/2 in. Deep, Five 1/2 in. KO

By Raco
Catalog # [8293](#)

4 in. Round Ceiling Pan, Drawn, 1/2 in. Deep, Five 1/2 in. KO

Features

- Rated for 50 lb fixture support
- Combination screw heads provide for faster installation
- L clamps provided for nonmetallic sheathed cable (NMSC)
- Supplied with five 1/2 in. knockouts
- 6.0 cu. in. capacity
- Do not use to support ceiling fans

General

Catalog Number	8293
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	4 in
Type	Ceiling Pan
UPC	050169002933

Dimensions

Actual Depth	0.56 in
Cubic Capacity	6 cu.in
Depth	0.5 in
Fixture Lbs.	50 lb
Height	4 in
Raised Ground	No
Weight	0.563 lb
Width	4 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
Description SPEC - Certification	Canada 1,324,360; Mexico 166,125.



Logistics

Carton Quantity	30
Packaging Type	No Packaging
Pallet Quantity	5250

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-8293-SPEC-EN | REV 6/2024