



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Two 1/2 in. KO's, AC/MC/Flex Clamps, Bar Hanger

By RACO
Catalog # [8325](#)

4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Two 1/2 in. KO's, AC/MC/Flex Clamps, Bar Hanger



Features

- Fixture bar hanger allows box to be located anywhere along length of bar
- Maximum support load for a static fixture is 50 lbs. when supported between 16 in. centers
- Cable clamps suitable for use with non-metallic sheathed cable
- 15.5 cu. in. capacity
- Not suitable for ceiling fan installations

Specifications

Certified Listed	cULus Listed
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Configuration

Knockouts	1/2 in
Bracket Type	No Bracket

Dimensions

Cubic Capacity	15.5 cu.in
Fixture Lbs.	10 lb.
Depth	1.5 in
Size	4 in

Actual Depth	2.132 in
Raised Ground	No
Width	14.5 in
Weight	0.924 lb.
Height	3.563 in

General

Wiring System	Armored Cable/Metal Clad/MCI-A/Flex
Ceiling Fan Rated	No
Color	Gray
Type	Box
Material	Steel
Drawn or Welded	Drawn
UPC	050169003251

Logistics

Packaging Type	No Packaging
Carton Quantity	25
Pallet Quantity	1650

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)