



3 in x 2 in. Switch Box, 2-27/32 in. Deep, One 1/2 in. KO & NMSC Clamps, S Bracket, Nails

By Raco
Catalog # 8355



3 in x 2 in. Switch Box, 2-27/32 in. Deep, One 1/2 in. KO & NMSC Clamps, S Bracket, Nails

Features

- 3 in. x 2 in., 2-27/32 in. deep
- L clamps provided for non-metallic sheathed cable (NMSC)
- Extra wide for ease of GFCI installation
- Gauging notches at 3/8 in., 1/2 in. and 5/8 in.
- Supplied with one 1/2 in. knockout
- Includes nails to fasten box to wood stud
- Non-gangable
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Switch Box
	Box
UPC	050169003558
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	3.032 in
Cubic Capacity	15.8 cu.in
Depth	2.84375 in
Height	3.625 in
Weight	0.704 lb
Width	3.5 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity	20
Packaging Type	No Packaging
Pallet Quantity	1800

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-1](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-8355-SPEC-EN | REV 6/2024