



## 3 in. x 2 in. Switch Box, Gangable, 2 in. Deep, Eight 1/2 in. KO's, Plaster Ears

By Raco  
Catalog # 8500



3 in. x 2 in. Switch Box, Gangable, 2 in. Deep, Eight 1/2 in. KO's, Plaster Ears

### Features

- 3 in. x 2 in., 2-1/2 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with eight 1/2 in. knockouts
- Plaster ears allow a box to be used in "old work" applications
- 12.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Type	No Bracket
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	Yes
Type	Switch Box
	Box
UPC	050169005002
Wiring System	Conduit

### Dimensions

Actual Depth	2.588 in
Cubic Capacity	12.5 cu.in
Depth	2.5 in
Height	4.192 in
Weight	0.525 lb
Width	2.154 in

### Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	2800

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978- 9](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-8500-SPEC-EN | REV 6/2024