



3 in. x 2 in. Switch Box, Gangable, 2-1/2 in. Deep, Three 1/2 in. KO & AC/MC/Flex Clamps, TS Bracket

By Raco
Catalog # 8524



3 in. x 2 in. Switch Box, Gangable, 2-1/2 in. Deep, Three 1/2 in. KO & AC/MC/Flex Clamps, TS Bracket

Features

- 3 in. x 2 in., 2-1/2 in. deep
- Includes TS side-mount bracket with gauging tabs and recessed nailing spurs
- BX clamps provided for steel & alum armored cable, MCI cable, MCI-A cable, and flexible conduit
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- Supplied with three 1/2 in. knockouts
- 12.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Catalog Number	8524
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	<ul style="list-style-type: none">• Switch Box• Box
UPC	050169005248
Wiring System	Armored Cable/Metal Clad/MCI-A/Flex

Dimensions

Cubic Capacity	12.5 cu.in
Depth	2.5 in
Height	7 in
Weight	0.711 lb
Width	2.203 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	2000

Product Assets

- [360 Product View - RACO_8524](#)
- [3D Product View - RACO_8524](#)
- [Catalogs - Steel Boxes, Covers and Accessories](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Sales Drawings - 8524 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 8524](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand