



## 4-11/16 in. Square Cover, Exposed Work, Toggle Switch/GFCI

By Raco  
Catalog # 858

4-11/16 in. Square Cover, Exposed Work, Toggle Switch/GFCI



### Features

- RACO® exposed work covers include required hardware for mounting the receptacle(s)
- RACO® exposed work covers meet the requirements of the 2014 NEC Article 250.146(A). No bonding jumper is required for covers with: (1) Crushed corners
- Hardware and cover are packed in a poly-bag with printed catalog number, compliances and installation instructions
- Cover includes captive mounting screws
- Cover made from zinc, pre-coated, steel
- 2 3/8 in. wide x 4 1/4 in. tall
- UPC bar-coded

### General

Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	858
Number of Gang(s)	2-Gang
Paintable/Stainable	No
Type	Exposed Cover
UPC	050169008584

### Dimensions

Cubic Capacity	10.3 cu.in
Dimensions	0.5 in x 4.688 in x 4.688 in
Height	4.688 in
Length	0.5 in
Weight	0.544 lb
Width	4.688 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Packaging Type	Polybag
Pallet Quantity	2880

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-17](#)  
[Certifications - UL COC - E195978-9](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-858-SPEC-EN | REV 6/2024