



# 4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Seven 3/4 in. KO's, Raised Ground

By Raco  
Catalog # 8663



4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Seven 3/4 in. KO's, Raised Ground

## Features

- Drawn construction
- 4 in. x 2 in., 1-7/8 in. deep
- Raised ground screw feature eliminates interference in surface mounting applications
- Supplied with seven 3/4 in. knockouts
- 13 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

## General

Bracket Type	No Bracket
Catalog Number	8663
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	3/4 in
Material	Steel
Number of Gang(s)	1-Gang
Type	Box
UPC	050169006634
Wiring System	Conduit

## Dimensions

Actual Depth	1.875 in
Cubic Capacity	13 cu.in
Depth	1.875 in
Height	4 in

Raised Ground	Yes
Weight	0.48 lb
Width	2.125 in

## Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed

## Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	3600

## Product Assets

[360 Product View - RACO\\_8663](#)  
[Catalogs - Steel Boxes, Covers and Accessories](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - NEMA OS1](#)  
[Certifications - LEED Statement](#)  
[Certifications - UL COC - E195978- 3](#)  
[Sales Drawings - RACO-drawn-steel-box-infographic](#)  
[SDS - HCC SDS](#)  
[Specifications - 8663](#)  
[Terms and Conditions - HCC Terms & Conditions](#)