



# 4-11/16 in. Square Work, Exposed Work, 30-50A Receptacle 2.141 in. Dia

By Raco  
Catalog # 878



4-11/16 in. Square Work, Exposed Work, 30-50A Receptacle 2.141 in. Dia

### Features

- RACO® exposed work covers include required hardware for mounting the receptacle(s)
- RACO® exposed work covers meet the requirements of the 2014 NEC Article 250.146(A). No bonding jumper is required for covers with: (1) Crushed corners
- Hardware and cover are packed in a poly-bag with printed catalog number, compliances and installation instructions
- Can be used as single-gang wall plate
- Cover includes captive screws, and rounded corners
- Cover made from zinc, pre-coated, steel
- Covers designed to match contours of handy box

### General

Catalog Number	878
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	878
Paintable/Stainable	Yes
Type	Exposed Cover
UPC	050169008782

### Dimensions

Cubic Capacity	10.3 cu.in
Dimensions	0.563 in x 4.69 in x 4.69 in
Height	4.69 in

Length	0.563 in
Weight	0.479 lb
Width	4.69 in

### Certifications And Compliance

Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2024)
Buy American Compliant Certified Listed	Yes <ul style="list-style-type: none"> <li>• cULus Listed</li> <li>•</li> </ul>

### Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Packaging Type	Polybag
Pallet Quantity	2880

### Product Assets

- [360 Product View - RACO\\_878](#)
- [3D Product View - RACO\\_878](#)
- [Catalogs - Steel Boxes, Covers and Accessories](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Sales Drawings - 878 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 878](#)
- [Terms and Conditions - HCC Terms & Conditions](#)