



## 4-11/16 in. Square Work, Exposed Work, 20A Receptacle 2.1594 in. Dia

By Raco  
Catalog # [887](#)

4-11/16 in. Square Work, Exposed Work, 20A Receptacle 2.1594 in. Dia



### Features

- RACO® exposed work covers include required hardware for mounting the receptacle(s)
- RACO® exposed work covers meet the requirements of the 2014 NEC Article 250.146(A). No bonding jumper is required for covers with: (1) Crushed corners
- Hardware and cover are packed in a poly-bag with printed catalog number, compliances and installation instructions
- Includes required hardware for mounting the receptacle
- Accepts single toggle switch and single 1.406 diameter receptacle
- 6.5 cu. in. capacity

### General

Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	887
Number of Gang(s)	2-Gang
Paintable/Stainable	No
Type	Exposed Cover
UPC	050169008874

### Dimensions

Cubic Capacity	10.3 cu.in
Dimensions	0.5 in x 4.688 in x 4.688 in
Height	4.688 in
Length	0.5 in
Weight	0.563 lb
Width	4.688 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Packaging Type	Polybag
Pallet Quantity	2880

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-887-SPEC-EN | REV 6/2024