



4-11/16 in. Square Work, Exposed Work, 30-60A Receptacle 2.625 in. Dia

By Raco
Catalog # 888

4-11/16 in. Square Work, Exposed Work, 30-60A Receptacle
2.625 in. Dia



Features

- RACO® exposed work covers include required hardware for mounting the receptacle(s)
- RACO® exposed work covers meet the requirements of the 2014 NEC Article 250.146(A). No bonding jumper is required for covers with: (1) Crushed corners
- Hardware and cover are packed in a poly-bag with printed catalog number, compliances and installation instructions
- Corners of cover are crushed to insure ground continuity when mounting on a box
- Device mounts to cover
- 6.5 cu. in. capacity

General

Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	888
Paintable/Stainable	No
Type	<ul style="list-style-type: none">• Exposed Cover• Exposed Cover
UPC	050169008881

Dimensions

Cubic Capacity	10.3 cu.in
Dimensions	0.5 in x 4.688 in x 4.688 in
Height	4.688 in
Length	0.5 in
Weight	0.45 lb
Width	4.688 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Packaging Type	Polybag
Pallet Quantity	2880

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-888-SPEC-EN | REV 6/2024