



KWIK-HANG® 4 in. Round Cover, Swivel for 3-1/2 in. or 4 in. Octagon Box, 1/2 or 3/4 in. Pipe

By Raco
Catalog # 894KH



KWIK-HANG® 4 in. Round Cover, Swivel for 3-1/2 in. or 4 in. Octagon Box, 1/2 or 3/4 in. Pipe

Features

- Swivel cover restricted to 20 degree swing from vertical
- KWIK-HANG® allows easy installation of high bay lighting fixtures. Fixture rests in position while wiring is completed
- Drawn construction
- Key-hole allows for installation of cover without removing the box screws
- 1-1/4 in. raised
- 16.0 cu. in. capacity

General

Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	Steel
Paintable/Stainable	Yes
Size	3.5 in;4 in
Type	Fixture Cover
UPC	050169608944

Dimensions

Dimensions	4 in x 4 in x 2 in
Fixture Lbs.	50 lb
Height	2 in
Length	4 in
Weight	0.614 lb
Width	4 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2275

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Sales Drawings - 894KH](#)
[SDS - HCC_SDS](#)
[Sell Sheets - Ball Type KWIK-HANG®](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: KWIK-HANG® Swivel Fixture Covers](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-894KH-SPEC-EN | REV 6/2024