



KWIK-BRACE® with 1-1/2 in. Deep Box for New Construction, Two 1/2 in. KO's

By Raco
Catalog # 926



KWIK-BRACE® with 1-1/2 in. Deep Box for New Construction,
Two 1/2 in. KO's

Features

- Slides apart to accommodate joist spacing from 16 in. to 24 in.
- Metal protection plate included
- Nail spurs for easy brace positioning
- #10-32, 1 in. long ceiling fan screws provided and #8-32 ceiling fixture mounting provisions
- Supplied with two 1/2 in. knockouts
- Easy installation, up front ground screw
- Easy to follow instructions and mounting hardware included

General

Ceiling Fan Rated	Yes
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Ceiling;Light
Knockouts	1/2 in
Material	Steel
Old Work or New Work	New Work
Size	4 in
Type	Box
UPC	050169009260

Dimensions

Ceiling Fan Lbs.	70 lb
Ceiling Fan Lbs., 16 in. Joist Span	70 lb
Ceiling Fan Lbs., 24 in. Joist Span	70 lb
Cubic Capacity	15.8 cu.in
Depth	1.5 in
Dimensions	15.13 in x 4.25 in x 3.03 in
Fixture Lbs.	90-210 lb
Fixture Lbs., 16 in. Joist Span	210 lb
Fixture Lbs., 24 in. Joist Span	90 lb
Height	3.03 in
Length	15.13 in
Raised Ground	Yes
Weight	2.333 lb
Width	4.25 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	6
Packaging Type	Box
Pallet Quantity	288

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Installation Manuals - RA-321 KWIK-BRACE Installation Instructions](#)
[Sales Drawings - 926](#)
[SDS - HCC_SDS](#)
[Sell Sheets - 4 in. Round Ceiling Fan-Rated Support with KWIK-BRACE® for New Work](#)
[Sell Sheets - RACO® Ceiling Fan Boxes](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO 926 KWIK-BRACE with Box](#)



