



GRID-BRACE™ with 4 in. Round Ceiling Box, 2-1/8 in. Deep, Two 1/2 & Four 1/2 & 3/4 in. Concentric KO's

By Raco
Catalog # 931



GRID-BRACE™ with 4 in. Round Ceiling Box, 2-1/8 in. Deep, Two 1/2 & Four 1/2 & 3/4 in. Concentric KO's

Features

- Heavy-duty GRID-BRACE® for 24 in spans
- Turnbuckle and 4 in chain section provided
- Yoke provided for threaded rod installation
- Mount box anywhere on sliding bracket
- Spacers provided for decorative ceiling tiles that are below the depth of metal grid for flush mounting of box
- #10-32 grade 5, 1 in ceiling fan screws included
- Easy to follow instructions included
- 70 lb. max support for fan or fixture

General

Catalog Number	931
Ceiling Fan Rated	Yes
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Ceiling;Light
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Material	Steel
Size	4 in
Suspended Ceiling	Yes
Type	Box
UPC	050169009314

Dimensions

Ceiling Fan Lbs.	70 lb
Cubic Capacity	22.3 cu.in
Depth	2.125 in
Dimensions	24.5 in x 6.75 in x 4.4 in
Fixture Lbs.	70 lb
Height	4.4 in
Length	24.5 in
Raised Ground	Yes
Weight	3.5 lb
Width	6.75 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	4
Pallet Quantity	80

Product Assets

[3D Product View - RACO_931](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Sales Drawings - 931](#)
[SDS - HCC_SDS](#)
[Sell Sheets - GRID-BRACE® Assembly](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: GRID-BRACE™](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-931-SPEC-EN | REV 6/2024