



RETRO-BRACE® with 1-1/2 in. Deep Box for Old Work, Two 1/2 in. KO's

By Raco
Catalog # 936



RETRO-BRACE® with 1-1/2 in. Deep Box for Old Work, Two 1/2 in. KO's

Features

- Adjustable for joist spacing from 16 in to 24 in
- Simple "tool free" expansion of brace
- #10-32, 1 in long ceiling fan screws provided and #8-32 ceiling fixture mounting provisions
- Supplied with two 1/2 in. knockouts
- Easy installation, up front ground screw
- Easy to follow instructions and mounting hardware included

General

Ceiling Fan Rated	Yes
Drawn or Welded	Drawn
EU RoHS Indicator	Yes
Fixture Type	Ceiling;Light
Knockouts	1/2 in
Material	Acier
Old Work or New Work	<ul style="list-style-type: none">• New Work• Old Work
Size	4 po
Type	<ul style="list-style-type: none">• Box• Boite
UPC	050169009369

Dimensions

Ceiling Fan Lbs.	35-70 lb
Ceiling Fan Lbs., 16 in. Joist Span	70 lb
Ceiling Fan Lbs., 24 in. Joist Span	35 lb
Cubic Capacity	15.8 cu.in
Depth	1.5 in
Dimensions	14 in x 4.22 in x 2.78 in
Fixture Lbs.	50-110 lb
Fixture Lbs., 16 in. Joist Span	110 lb
Fixture Lbs., 24 in. Joist Span	50 lb
Height	2.78 in
Length	14 in
Raised Ground	Yes
Weight	2.242 lb
Width	4.22 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	6
Pallet Quantity	312

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 936](#)
[SDS - HCC_SDS](#)
[Sell Sheets - RACO® Ceiling Fan Boxes](#)
[Sell Sheets - 4 in. Round Ceiling Fan-Rated Support with RETRO-BRACE®](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: Choosing the Correct Ceiling Fan Box](#)
[Video - RACO: RETRO-BRACE® Old-Work Ceiling Fan Support](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-936-SPEC-EN | REV 6/2024

