



## 2-Gang Box, Welded, 2-1/2 in. Deep, Eight 3/4 & 1 in. Concentric KO's, Three 1/2 in. KO's, and Six 3/4 in. KO's

By Raco  
Catalog # 941



2-Gang Box, Welded, 2-1/2 in. Deep, Eight 3/4 & 1 in. Concentric KO's, Three 1/2 in. KO's, and Six 3/4 in. KO's

### Features

- Gang boxes save time in installation, no need to gang boxes together.
- Have 3/4" and 1" concentric KO's for use with a wide variety of wiring methods.
- Bottom KO pattern, 3-1/2" and 2-3/4" at either end of box.
- Accepts two styles of covers, flat and 3/4" raised device cover.
- Use low voltage partitions #947 or #949.
- Used where multiple wiring devices are to be centrally located
- Bottom knockouts are at either end of box
- 70.0 cu. in. capacity
- Used in finish wall applications

### General

Bracket Type	No Bracket
Catalog Number	941
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in;3/4 in;3/4-1 in Concentric
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169009413
Wiring System	Conduit

### Dimensions

Cubic Capacity	70 cu.in
Depth	2.5 in
Height	4.5 in
Weight	1.625 lb
Width	6.813 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	5
Pallet Quantity	600

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-1](#)  
[Sales Drawings - 941 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-941-SPEC-EN | REV 6/2024