



# 3-Gang Box, Welded, 2-1/2 in. Deep, Six 3/4 & 1 in. Concentric KO's, Six 1/2 in. KO's, and Twelve 3/4 in. KO's

By Raco  
Catalog # 942

3-Gang Box, Welded, 2-1/2 in. Deep, Six 3/4 & 1 in. Concentric KO's, Six 1/2 in. KO's, and Twelve 3/4 in. KO's

## Features

- Gang boxes save time in installation, no need to gang boxes together.
- Have 3/4" and 1" concentric KO's for use with a wide variety of wiring methods.
- Bottom KO pattern, 3-1/2" and 2-3/4" at either end of box.
- Accepts two styles of covers, flat and 3/4" raised device cover.
- Use low voltage partitions #974 or #949.
- Used where multiple wiring devices are to be centrally located
- Bottom knockouts are at either end of box
- 90.0 cu. in. capacity
- Used in finish wall applications

## General

Bracket Type	No Bracket
Catalog Number	942
Color	Gray
EU RoHS Indicator	Yes
Knockouts	1/2 in;3/4 in;3/4-1 in Concentric
Material	Steel
Number of Gang(s)	3-Gang
Type	Box
UPC	050169009420



## Wiring System

Conduit

## Dimensions

Cubic Capacity	90 cu.in
Depth	2.5 in
Height	4.5 in
Weight	1.975 lb
Width	8.625 in

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed

## Logistics

Carton Quantity	5
Pallet Quantity	440

## Product Assets

- [Catalogs - Steel Boxes, Covers and Accessories](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - UL COC - E195978-1](#)
- [Sales Drawings - 942 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 942](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand