



4-Gang Box, Welded, 2-1/2 in. Deep, Eight 3/4 & 1 in. Concentric KO's, Six 1/2 in. KO's, and Eight 3/4 in. KO's

By Raco
Catalog # [943](#)



4-Gang Box, Welded, 2-1/2 in. Deep, Eight 3/4 & 1 in. Concentric KO's, Six 1/2 in. KO's, and Eight 3/4 in. KO's

Features

- Gang boxes save time in installation, no need to gang boxes together.
- Have 3/4" and 1" concentric KO's for use with a wide variety of wiring methods.
- Bottom KO pattern, 3-1/2" and 2-3/4" at either end of box.
- Accepts two styles of covers, flat and 3/4" raised device cover.
- Use low voltage partitions #947 or #949.

General

Bracket Type	No Bracket
EU RoHS Indicator	Yes
Knockouts	1/2 in;3/4 in;3/4-1 in Concentric
Material	Steel
Number of Gang(s)	4-Gang
Type	Box
UPC	050169009437
Wiring System	Conduit

Dimensions

Cubic Capacity	110 cu.in
Depth	2.5 in
Height	4.5 in
Weight	2.313 lb
Width	10.438 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	5
Pallet Quantity	320

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-1](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-943-SPEC-EN | REV 6/2024