



## 4-Gang Box, Welded, 1-5/8 in. Deep, Sixteen 1/2 & 3/4 in. Concentric KO's, Six 1/2 in. KO's, and Four 3/4 in. KO's

By Raco  
Catalog # 953



4-Gang Box, Welded, 1-5/8 in. Deep, Sixteen 1/2 & 3/4 in. Concentric KO's, Six 1/2 in. KO's, and Four 3/4 in. KO's

### Features

- Gang boxes save time in installation, no need to gang boxes together.
- Have 1/2" and 3/4" concentric KO's for use with a wide variety of wiring methods.
- Bottom KO pattern, 3-1/2" and 2-3/4" at either end of box.
- Accepts two styles of covers, flat and 3/4" raised device cover.
- Use low voltage partitions #947 or #949.
- Spacing of devices match standard wall plates
- Used where multiple wiring devices are to be centrally located
- Supplied with sixteen (16) 1/2 & 3/4 in. concentric knockouts
- 3/4 in. raised mud rings and flat covers available for all sizes
- 72.8 cu. in. capacity

### General

Bracket Type	No Bracket
Catalog Number	953
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in;3/4 in;1/2-3/4 in Concentric
Material	Steel
Number of Gang(s)	4-Gang
Type	Box
UPC	050169009536
Wiring System	Conduit

### Dimensions

Actual Depth	1.89 in
Cubic Capacity	72.8 cu.in
Depth	1.625 in
Height	4.53 in
Weight	1.765 lb
Width	10.49 in

### Certifications And Compliance

Certified Listed                      UL Listed

### Logistics

Carton Quantity                      5  
Pallet Quantity                      720

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-1](#)  
[Sales Drawings - 953 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-953-SPEC-EN | REV 6/2024