



6-Gang Box, Welded, 1-5/8 in. Deep, Twenty 1/2 & 3/4 in. Concentric KO's, Six 1/2 in. KO's, and Four 3/4 in. KO's.

By Raco
Catalog # [955](#)



6-Gang Box, Welded, 1-5/8 in. Deep, Twenty 1/2 & 3/4 in. Concentric KO's, Six 1/2 in. KO's, and Four 3/4 in. KO's.

Features

- Gang boxes save time in installation, no need to gang boxes together
- 1/2 in. and 3/4 in. concentric KO's for use with a wide variety of wiring methods
- Bottom KO pattern, 3-1/2 in. and 2-3/4 in. at either end of box
- Accepts two styles of covers, flat and 3/4 in. raised device cover
- Use low voltage partitions #947 or #949

General

Bracket Type	No Bracket
Knockouts	1/2 in.;3/4 in.;1/2-3/4 in Concentric
Material	Steel
Type	Box
UPC	050169895504

Dimensions

Cubic Capacity	98.5 cu.in
Depth	1.625 in
Height	4.5 in
Weight	2.45 lb
Width	14.063 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	1
Pallet Quantity	304

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-1](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-955-SPEC-EN | REV 6/2024