



## 3-Gang Wallbox, Gangable, 4-inch Deep, 2-inch Knockouts

By Raco  
Catalog # 986



3-Gang Wallbox, Gangable, 4-inch Deep, 2-inch Knockouts

### Features

- Knockouts from 1/2" up to 2"
- 4" depth accepts any device
- Concentric 1/2" - 3/4" knockouts for pre-connectorized AV cables
- Eccentric 1/2" - 3/4" knockouts
- Raised ground provision in each gang
- Accepts low voltage partition
- NEMA spaced device mounting, accepts industry standard wallplates
- Adjustable stud mounting brackets built in to accommodate different stud and sheetrock thickness
- Adjustable far side support
- Suitable for masonry application

### General

Catalog Number	986
Drawn or Welded	Welded
Material	Steel
Number of Gang(s)	3-Gang
Type	Large Capacity
UPC	050169009864
Wiring System	Conduit

### Dimensions

Actual Depth	4.165 in
Cubic Capacity	79 cu.in
Depth	4
Height	4.205 in
Weight	2.166 lb
Width	7.374 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	6
Packaging Type	No Packaging
Pallet Quantity	336

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Sales Drawings - 986 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - AV Wall Boxes Gangable, 4" Deep](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-986-SPEC-EN | REV 6/2024