



#12 Stranded Insulated Copper Wire Pigtail, 8 in. Length (100/BE)

By Raco
Catalog # 993



#12 Stranded Insulated Copper Wire Pigtail, 8 in. Length (100/BE)

Features

- RACO® 6" and 8" ground pigtails feature 4-way slotted, phillips, hex-head) combo 10-32 captive screws
- #12 stranded insulated wire with spade terminal
- Captive 4-way combo head ground screw
- 8 in. wire length
- Suitable for 10-32 threaded hole

General

Accessory Type	Box
EU RoHS Indicator	Contact Manufacturer
Type	Ground Screws
UPC	050169009932

Dimensions

Dimensions	8 in x 0.4 in x 0.5 in
Height	0.5 in
Length	8 in
Weight	0.028 lb
Width	0.4 in

Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Packaging Type	Bundle
Pallet Quantity	50000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-993-SPEC-EN | REV 6/2024