



# 1-1/4 in. Rigid/IMC Compression Coupling

By Raco  
Catalog # 1825

1-1/4 in. Rigid/IMC Compression Coupling

## Features

- All steel/malleable iron construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- Hex compression nuts assure easy wrench installation
- Available in trade sizes 1/2 in. through 4 in.

## General

Catalog Number	1825
Conduit Type	Rigid/IMC
Connector Type	Compression
EU RoHS Indicator	Yes
Fitting Type	Couplings
Material	Steel/Malleable Iron
UPC	050169018255

## Dimensions

Dimensions	1.938 in x 1.953 in x 1.953 in
Height	1.953 in
Length	1.938 in
Trade Size	1-1/4 in
Weight	0.849 lb



Width	1.953 in
-------	----------

## Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1330

## Product Assets

- Catalogs - [RACO / TayMac / Bell Full Catalog](#)
- Catalogs - [Commercial Fittings](#)
- Certifications - [UL COC - E195969- 1](#)
- Product Logo - [Conduit](#)
- Sales Drawings - [1825 Customer Drawing](#)
- SDS - [HCC SDS](#)
- Specifications - [1825 Specification Sheet French](#)
- Specifications - [1825 Specification Sheet](#)
- Specifications - [1825](#)
- Terms and Conditions - [HCC Terms & Conditions](#)