



Vapor Barrier Ceiling Box, 4" Round, Non-Metallic, 2028FBAR

By TradeSelect (Temco)

Catalog # [2028FBAR](#)

Vapor Barrier Ceiling Box, 4" Round, Non-Metallic



Features

- Self-clamping wire entry clamps
- Vapour/air barrier flange and integral wire entry seal provides superior energy savings and quick installation
- Hands free installation for 1/2", 5/8", or 3/4" drywall
- Front mounted grounding screw with combination straight/Robertson head

Specifications

Certified Listed CSA

Configuration

Bracket Setback 0.50

Dimensions

Fixture Lbs. 50 lb.
Depth 2.625 in
Actual Depth 2.625 in
Width 5.25 in
Weight .265 lb.

Height 7 in

General

Wiring System Nonmetallic Sheathed Cable
Style Vapor Barrier
Color Yellow
Type

- Vapor Barrier Box
- Box

Cable Clamps 4
Material Thermoplastic Resin
UPC 805035054536
Volume 28.1

Logistics

Carton Quantity 40
Pallet Quantity 640

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)
[Catalog Page \[English\]](#)