



3 in. EMT or Rigid/IMC Set-Screw Coupling

By Raco
Catalog # 2152

3 in. EMT or Rigid/IMC Set-Screw Coupling

Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Tri-head screws may be installed using slotted, Phillips, or Robertson head screwdriver
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Catalog Number	2152
Conduit Type	EMT
Connector Type	Set-Screw
EU RoHS Indicator	Yes
Fitting Type	Couplings
Material	Steel
UPC	050169021521

Dimensions

Dimensions	4.331 in x 3.776 in x 3.776 in
Height	3.776 in
Length	4.331 in
Trade Size	3 in
Weight	1.843 lb



*Representative Image

Width	3.776 in
-------	----------

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	800

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Certifications - UL COC - E195969- 1](#)
[Certifications - UL COC - E195970 - 1](#)
[Product Logo - Conduit](#)
[Sales Drawings - 2152-CHINA Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 2152 Specification Sheet](#)
[Specifications - 2152 Specification Sheet English](#)
[Specifications - 2152 Specification Sheet French](#)
[Terms and Conditions - HCC Terms & Conditions](#)