



# 1/2 in. EMT Raintight Compression Connector, Insulated

By Raco  
Catalog # 2912RT

1/2 in. EMT Raintight Compression Connector, Insulated.

## General

|                          |                      |
|--------------------------|----------------------|
| Catalog Number           | 2912RT               |
| Conduit Type             | EMT                  |
| Connector Type           | Compression          |
| EU RoHS Indicator        | Contact Manufacturer |
| Environmental Conditions | Wet Location         |
| Fitting Type             | Connectors           |
| Insulation Type          | Insulated            |
| Material                 | Steel                |
| UPC                      | 050169291290         |

## Dimensions

|            |                              |
|------------|------------------------------|
| Dimensions | 1.621 in x 1.05 in x 1.12 in |
| Height     | 1.12 in                      |
| Length     | 1.621 in                     |
| Trade Size | 1/2 in                       |
| Weight     | 0.1 lb                       |
| Width      | 1.05 in                      |



\*Representative Image

## Certifications And Compliance

|                      |              |
|----------------------|--------------|
| Certified Listed     | cULus Listed |
| Industry Standard(s) | UL 514B      |

## Logistics

|                 |       |
|-----------------|-------|
| Carton Quantity | 250   |
| Pallet Quantity | 15000 |

## Product Assets

- [Brochures - HCC Products for Solar](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - UL COC - E195970 - 2](#)
- [Product Logo - Conduit](#)
- [Sales Drawings - 2912RT-CHINA Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Raintight Steel EMT Compression Fittings](#)
- [Specifications - 2912RT Specification Sheet French](#)
- [Specifications - 2912RT](#)
- [Terms and Conditions - HCC Terms & Conditions](#)