



1 in. EMT Raintight Compression Connector, Insulated

By Raco
Catalog # 2914RT



1 in. EMT Raintight Compression Connector, Insulated.

*Representative Image

General

Catalog Number	2914RT
Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	Steel
UPC	050169291498

Dimensions

Dimensions	1.853 in x 1.56 in x 1.645 in
Height	1.645 in
Length	1.853 in
Trade Size	1 in
Weight	0.216 lb
Width	1.56 in

Certifications And Compliance

Certified Listed Industry Standard(s)	cULus Listed UL 514B
---------------------------------------	----------------------

Logistics

Carton Quantity	75
Minimum Pack Quantity	15
Pallet Quantity	6000

Product Assets

- [Brochures - HCC Products for Solar](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - UL COC - E195970 - 2](#)
- [Product Logo - Conduit](#)
- [Sales Drawings - 2914RT-CHINA Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Raintight Steel EMT Compression Fittings](#)
- [Specifications - 2914RT Specification Sheet French](#)
- [Specifications - 2914RT](#)
- [Terms and Conditions - HCC Terms & Conditions](#)