



## 1 in. EMT Raintight Compression Coupling

By Raco  
Catalog # [2924RT](#)

1 in. EMT Raintight Compression Coupling.



\*Representative Image

### General

Catalog Number	2924RT
Conduit Type	EMT
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Couplings
Material	Steel
UPC	050169292495

Certified Listed  
Industry Standard(s)

cULus Listed  
UL 514B

### Logistics

Carton Quantity	75
Minimum Pack Quantity	15
Pallet Quantity	4500

### Product Assets

<a href="#">Brochures - HCC Products for Solar</a>	
<a href="#">Catalogs - RACO / TayMac / Bell Full Catalog</a>	
<a href="#">Certifications - UL COC - E195970 - 2</a>	
<a href="#">Product Logo - Conduit</a>	
<a href="#">Sales Drawings - 2924RT-CHINA Customer Drawing</a>	
<a href="#">SDS - HCC SDS</a>	
<a href="#">Sell Sheets - Raintight Steel EMT Compression Fittings</a>	
<a href="#">Specifications - 2924RT Specification Sheet French</a>	
<a href="#">Specifications - 2924RT</a>	
<a href="#">Terms and Conditions - HCC Terms &amp; Conditions</a>	

### Dimensions

Dimensions	2.237 in x 1.56 in x 1.645 in
Height	1.645 in
Length	2.237 in
Trade Size	1 in
Weight	0.271 lb
Width	1.56 in

### Certifications And Compliance



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO\_CA-2924RT-SPEC-EN | REV 10/2024