



# 3 in. Flex Squeeze Connector, Insulated

By Raco  
Catalog # 3212



3 in. Flex Squeeze Connector, Insulated

## Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

## General

Catalog Number	3212
Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169032121

## Dimensions

Dimensions	8.969 in x 5.063 in x 6.54 in
------------	-------------------------------

Height	6.54 in
Length	8.969 in
Trade Size	3 in
Weight	5.58 lb
Width	5.063 in

## Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	224

## Product Assets

- [Catalogs - Commercial Fittings](#)
- [Product Logo - MC\\_BX\\_CONDUIT LOGO](#)
- [SDS - HCC SDS](#)
- [Specifications - 3212](#)
- [Specifications - 3212 Specification Sheet](#)
- [Specifications - 3212 Specification Sheet French](#)
- [Terms and Conditions - HCC Terms & Conditions](#)