



# 3/4 in. Flex Straight Squeeze Connector, Insulated

By Raco  
Catalog # 3303



3/4 in. Flex Straight Squeeze Connector, Insulated

## Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

## General

Catalog Number	3303
Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Insulated
Item Type	4D
Material	Malleable Iron
UPC	050169033036

## Dimensions

Dimensions	1.469 in x 1.38 in x 1.938 in
------------	-------------------------------

Height	1.938 in
Length	1.469 in
Trade Size	3/4 in
Weight	0.228 lb
Width	1.38 in

## Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	14400

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Customer Notices - Prop 65 Notice](#)
- [SDS - HCC SDS](#)
- [Specifications - 3303 Specification Sheet French](#)
- [Specifications - 3303 Specification Sheet](#)
- [Specifications - 3303](#)
- [Terms and Conditions - HCC Terms & Conditions](#)